

ORDERING INFORMATION

Order code: 69287
Description: F54T5/41K/8/H0/PS/G5/ELUME S2
UPC: 069549025974
Case quantity: 25

PERFORMANCE DATA


Shape: T5
Base: G5 (Min Bipin)
Starting method: Program Start (PS)
Wattage (W): 54
Colour temperature (K): 4 100
CRI: 85
Rated life on PS/PRS¹ ballast:
 Based on a 3 hour start 30 000
 Based on a 12 hour start 40 000
Initial lumens (lm): 5 000
Mean lumens (lm): 4 683
Nominal efficiency (lm/W): 93
TCLP compliant: Yes
Phosphor composition: Triphosphor
Nominal lamp operating frequency (Hz): 60
² Minimum starting temperature (°C): -10




Nominal length : 46 in. (1 168 mm)
 Dia. : 5/8 in. (16 mm)

¹ The life rating indicated is based on 3 hour burning cycles under specified conditions and with ballast meeting ANSI specifications.
² The minimum starting temperature is a function of the ballast.

DIMENSIONS



SPECTRAL DISTRIBUTION



E Means this bulb meets federal minimum efficiency standards.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

STANDARD®