

Project Name

Location

Prepared By



SATCO S11580

5.5PAR20/LED/5CCT/SP/120V

Notes

[www] 11-20-2023 01:02:46

General

Status	Active
Watts	5.5W
Incandescent Equivalent	50W
Fluorescent Equivalent	11W
Volts	120V
Shape	PAR20
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	90
Lumens	500L
Beam Spread	25
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	1255
Spot Type	SP - Spot
Power Factor	0.7
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	3.19
MOD	2.48
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Housing Color	Silver
Weight (lb.)	0.1

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

