SATCO NUVO

Project Name

Location

Prepared By



Notes

General	
Status	Active
Watts	11W
Incandescent Equivalent	75W
Fluorescent Equivalent	15W
Volts	120V
Shape	PAR30SN
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	90
Lumens	1000L
Beam Spread	60
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED
Electrical	

Electrical	
Operating Frequency	60Hz
CBCP	834
Spot Type	WFL - Wide Flood
Power Factor	0.9
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical	
MOL	3.62
MOD	3.74
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Housing Color	Silver
Weight (lb.)	0.24

Additional Information	
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

Compliance	
Safety Listing	cULus - Listed
Location Rating	Wet
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED Lamp







