

# LOW VOLTAGE CYLINDERS

## TL201

### Features:

Lamp: MR16 12V/50W (max.)  
Clear tempered glass bulb cover lens  
with UV protection provided  
Finishes: Brushed Steel (BST), Oil Rubbed  
Bronze (ORB)

### Specifications:

Gimball Ring Dia.: 2.5"  
OAH: 5" (max.)



TL201-BST



TL201-ORB

## TL101

### Features:

Lamp: MR16 12V/50W (max.)  
Clear tempered glass bulb cover lens  
with UV protection provided  
Finishes: Oil Rubbed Bronze (ORB),  
White (WH)

### Specifications:

Head length: 4"  
Dia.: 2.5"  
OAH: 6.5" (max.)



TL101-ORB



TL101-WH

## TL901

### Features:

Lamp: MR16 12V/50W (max.)  
Clear tempered glass bulb cover lens  
with UV protection provided  
Finishes: Brushed Steel (BST), Oil Rubbed  
Bronze (ORB)

### Specifications:

Head length: 3"  
Width: 2.25"  
OAH: 6.5" (max.)



TL901-BST



TL901-ORB