

## FLEXIBLE CONDUIT FOR HAK-C-100 AND C75-100-A

nVent RAYCHEM HCTE-1000 is a helical flexible plastic tubing for C75-100-A and HAK-C-100 connection kits.



### FEATURES

High crush resistance

Highly flame retardant

Fluid resistant

Simple and fast to install

Reliable during long life: 10 year product warranty available, maintenance free

### SPECIFICATIONS

Table 1/1						
Catalog Number	Item Name	Material	Operating Temperature	Outer Diameter	Inner Diameter	Wall Thickness
3679754004	HCTE-1000-0-SP	Modified Ethylene Tetrafluoroethylene	-67 to 392 °F	1.226 in	0.975 in	0.023 in max

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)**Europe, Middle East, Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**

**TRACER**

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.