

Model	Smoke Sensor	Battery Type	Electrochemical CO Sensor	Voice Location	Latching Alarm Indicator	End-of-Life Signal	Single Test/Silence Button	Limited Warranty
120V Hardwired (Includes Battery Backup If Listed Under Battery Type)								
► 7030BSLA (1038871)	Photo/Strobe/CO	10-Year Sealed Lithium	✓		✓	✓	✓	10 Years
► SC9120BA	Ion	9V Alkaline	✓		✓	✓	✓	10 Years
SC9120LBLA	Ion	10-Year Lithium	✓		✓	✓	✓	10 Years
SC9126BTCA	Ion	9V Alkaline	✓		✓	✓	✓	10 Years
SC7010BA	Photo	Two AA Alkaline	✓		✓	✓	✓	7 Years
SC7016BTCA	Photo	Two AA Alkaline	✓		✓	✓	✓	7 Years
SC7010BVA	Photo	Two AA Alkaline	✓	✓	✓	✓	✓	10 Years
Battery Operated								
PRC700A-6 (1039778)	Photo	Two AA Alkaline	✓			✓	✓	7 Years
PRC700VA-6 (1039781)	Photo	Two AA Alkaline	✓	✓		✓	✓	7 Years
PRC710A-6 (1039860)	Photo	10-Year Sealed Lithium	✓			✓	✓	10 Years
PRC710VA-6 (1039862)	Photo	10-Year Sealed Lithium	✓	✓		✓	✓	10 Years
Wireless Interconnect								
SC0500NVA (1039823) (Battery Operated)	Photo	Two AA Alkaline	✓		✓	✓	✓	7 Years
Connected Safety								
1042253 (Battery Operated)	Photo	First Alert 3 Cell Lithium	✓	✓		✓	✓	5 Years

COMBINATION ALARMS

FEATURED PRODUCTS



► 7030BSLA (1038871)

Hardwired 3-in-1 Smoke, Carbon Monoxide & LED Strobe Alarm with 10-Year Sealed Lithium Battery Backup

- Photoelectric Smoke Sensing Technology
- Electrochemical Carbon Monoxide Sensor
- 10-Year Sealed Lithium Battery Backup
- Smart LED Strobe - Separate Flash Patterns for Smoke and Carbon Monoxide
- 10-Year Limited Warranty



► SC9120BA

Hardwired Ion Smoke & Carbon Monoxide Combination Alarm with Battery Backup

- Ionization Smoke Sensing Technology
- Electrochemical Carbon Monoxide Sensor
- Two Latching Features – Alarm Latch: Remembers and Identifies Initiating Alarms; Low Battery: Identifies Affected Unit
- Perfect Mount - Allows for Easy Alignment of Alarm
- 10-Year Limited Warranty

CARBON MONOXIDE ALARMS	Model	Battery Type	Electrochemical CO Sensor	Digital Display	Latching Alarm Indicator	End-of-Life Signal	Single Test/Silence Button	Limited Warranty	
	120V Hardwired (Includes Battery Backup If Listed Under Battery Type)								
	► C05120BNA	9V Alkaline	✓		✓	✓	✓	7 Years	
	Battery Operated								
	► C0400A (1039934)	Two AA Alkaline	✓			✓	✓	7 Years	
	C04106A (1039724)	Two AA Alkaline	✓	✓		✓	✓	7 Years	
	C0710A (1039749)	10-Year Sealed Lithium	✓	✓		✓	✓	10 Years	
	Plug-in (Includes Battery Backup If Listed Under Battery Type)								
	C0600A (1039196)	Plug-in ONLY	✓			✓	✓	7 Years	
	C0605A (1039731)	Two AA Alkaline	✓			✓	✓	7 Years	
C0615A (1039742)	Two AA Alkaline	✓	✓		✓	✓	7 Years		
GC016CNA (1039758) (Explosive Gas/CO Combo Alarm)	9V Alkaline	✓	✓		✓	✓	5 Years		

LED STROBES	Model	Smoke Sensor	Battery Type	Electrochemical CO Sensor	Latching Alarm Indicator	End-of-Life Signal	Single Test/Silence Button	Limited Warranty	
	120V Hardwired (Includes Battery Backup If Listed Under Battery Type)								
	7020BSLA (1036168)	Photo/Strobe	10-Year Sealed Lithium		✓	✓	✓	10 Years	
	7030BSLA (1038871)	Photo/Strobe/CO	10-Year Sealed Lithium	✓	✓	✓	✓	10 Years	
	Strobe Only								
	SLED177A (1038604)	Strobe ONLY	Hardwired ONLY					10 Years	


FEATURED PRODUCTS



- **C05120BNA**
Hardwired Carbon Monoxide Alarm with Battery Backup
- Electrochemical Carbon Monoxide Sensor
 - 9V Alkaline Battery Backup
 - Two Latching Features – Alarm Latch: Remembers and Identifies Initiating Alarms; Low Battery: Identifies Affected Unit
 - End-of-Life Signal
 - 7-Year Limited Warranty



- **C0400A (1039934)**
Battery Operated Carbon Monoxide Alarm
- Electrochemical Carbon Monoxide Sensor
 - Two AA Batteries
 - Two Silence Features – Silences Low Battery Chirps for Up to Eight Hours or Temporarily Silences Nuisance Alarms
 - End-of-Life-Signal
 - 7-Year Limited Warranty

FIRE EXTINGUISHERS	Model	ULC Rating	Fights	Commercial Grade Metal Valve	Pin Pressure Gauge	Mounting Bracket	Meets DOT Requirements	Coast Guard Approved	Limited Warranty	
	Rechargeable Multi-Purpose									
	▶ FE1A10GOA	1-A:10-B:C	▲ B C	✓	✓	✓	✓	✓	10 Years	
	FE3A40A	3-A:40-B:C	▲ B C	✓	✓	✓	✓	✓	12 Years	
	Kitchen-Use									
	KFE5-A	5-B:C	B C			✓	✓		10 Years	
	Intuitive to use - great for under kitchen cabinet storage!									
	▶ EZ Fire Spray (1043283)		▲ B C						3 Years	
										

FEATURED PRODUCTS



- ▶ **EZ Fire Spray (1043283)**
- Perfect for Apartments, Home, Auto and Marine
 - Intuitive to Use – Familiar Spray Can Form
 - Easy Clean-Up – Reduces Maintenance and Clean-Up Costs
 - No Hazmat Fees
 - Product Comes in a 4-Piece Tray
 - 3-Year Limited Warranty



- ▶ **FE1A10GOA**
- Multi-Purpose Fire Extinguisher**
- 2.5lb Fire Extinguisher
 - Rated 1-A:10-B:C
 - Rechargeable
 - Bracket With Strap for Easy Mounting
 - 10-Year Limited Warranty



- ▶ **RM4**
- 120V AC Smart Relay**
- Works With BRK Smoke and Heat Alarms and Smart Interconnect BRK CO Alarms
 - Form-C Contacts That Switch Between Normally Open and Closed Contacts
 - Maximum Contact Rating: 120-Volt AC and 30-Volt DC; Resistive-15 Amps; Motor-1/3 Horsepower
 - 10-Year Limited Warranty



- ▶ **ADK-12**
- Conversion Adapter**
- Easily Convert From Competitive Alarms Without Rewiring
 - Saves Time and Installation Costs
 - Perfect for Retrofit or Remodel Jobs
 - For Use With Select Kidde® Models

MISCELLANEOUS	Model	Description	Features
	▶ ADK-12	Adapter Plug	Easily connect competitive alarms without rewiring; for use with Kidde smoke alarms; perfect for retrofit applications
	1047153	Escape Ladder - 2 Story	Strong steel construction; large hooks secure easily to window sills; slip-resistant rungs; DuPont™ Cordura® - Nylon Strapping; fully assembled and ready to use; 6-Year Limited Warranty
	1047154	Escape Ladder - 3 Story	Strong steel construction; large hooks secure easily to window sills; slip-resistant rungs; DuPont™ Cordura® - Nylon Strapping; fully assembled and ready to use; 6-Year Limited Warranty
	HD6135FB	120V AC 135°F Fixed Rate Heat Alarm	135°F Fixed temperature; bi-metal switch sensor; for applications not suitable for smoke alarms; 10-Year Limited Warranty
	PSM1A	Interconnect Module (Pull Station & Flow Switch)	Interconnects and activates smoke alarms on activation of fire pull stations, sprinkler flow switches, etc.; 5-Year Limited Warranty
	RDA	Radon Test Kit	Everything included for a complete mail-in radon test; kit includes all test materials, manual and preprinted return envelope; \$17 USD lab fee not included; 1-Year Limited Warranty
	▶ RM4	BRK 120V AC Smart Relay	Works with BRK Smoke and Heat Alarms and Smart Interconnect BRK CO Alarms; 120-volt AC-powered; Form-C contacts that switch between normally open and closed contacts; maximum contact rating: 120-volt AC and 30-volt DC, Resistive-15 amps, Motor 1/3 horsepower; 10-Year Limited Warranty