

Eaton AH1258BK-F

Catalog Number: AH1258BK-F

Recp Sgl Flush 50A 125/250V 3P4W Str BK: AH1258BK-F



General specifications

Product Name	Catalog Number
Eaton Arrow Hart power device receptacle	AH1258BK-F
	UPC
	032664006388
Product Length/Depth	Product Height
2.112 in	3.688 in
Product Width	Product Weight
2.455 in	0.35 lb

Warranty

Refer to warranty document.

Product specifications

Special features

Range receptacle

Color

Black

Wiring method

Back

Features

Range receptacle

Mounting method

Flush

Amperage Rating

50A

Number Of Poles

Three-pole

Base color

Black

Type

Flush mount receptacle

NEMA configuration

14-50R

Design type

Receptacle

Connection type

Screw

Style

Power

Number of wires

4

Receptacle type

Three-pole, four-wire, grounding

Voltage rating

125/250V

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Specifications and datasheets

[FMR NEMA 14-30, 14-50 spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)