

## CAN-TWIST™ WIRE CONNECTORS

- **“One Size Fits All” - Canada’s Best Selling Connector!**
- Exceptional wire-range capacity - listed for over 400 different wire combinations from 22 to 8 AWG (solid and/or stranded)
- Ergonomic, easy-twist design - only a few turns are needed to achieve torque, without the need to pre-twist wire
- Heat-set, square-cut springs stay in place, and firmly grip wire for superior connectivity
- Flexible outer shell virtually eliminates cracking, expanding to securely accommodate wire - indicated by white expansion lines
- Extended skirt length provides over-strip protection
- Sleek design helps reduce box fill



CSA 22.2 #188 Certified  
20amp / 600V  
Operating temperature:  
up to 105 °C / 221 °F

### PACKAGE DETAILS

	CAT #
C-Pak of 100 Connectors	30-207
Jar of 175 Connectors	30-107J
Jar of 475 Connectors	30-307J
Bag of 500 Connectors	30-607
Jar of 1,000 Connectors	30-707J
Stubby Barrel of 7,500 Connectors	30-817
Barrel of 25,000 Connectors	30-807

## CAN-SNAP™ NON-METALLIC FITTINGS

Can-Snap provides exceptional performance, and incredible value! Installed quickly and easily, without the use of tools, Can-Snap secures cable in place, providing superior protection from damage caused by rough knock-out edges.

- Quick and easy installation - simply push in, no tools required
- Protects and secures cable
- Proudly made in Canada!

### CABLE SIZES

- 1/2" (Blue): 14/2, 14/3, 12/2, 10/2
- 3/4" (Red): 8/3, 6/3



1/2" Size: CSA Certified / UL Listed  
3/4" Size: CSA Certified

### 1/2" (BLUE)

	CAT #
Jar of 250	91-720J
Jar of 125	91-710J
Jar of 50	91-700J
Stubby of 2,500	91-740
Barrel of 10,000	91-750

### 3/4" (RED)

Jar of 50	91-800J
-----------	---------

# WIRE TERMINATION