

PAR



| HH Item # Part # | Description (LED Wattage) | Bulb Shape | Bulb Base | Colour (Temp.) | Beam Degree | Lumens | Hours | Dim. | E-Star |
|---------------------|------------------------------|---------------|--------------|-----------------------------|----------------|--------|-------|------|---|
| 471250 | LED 50W Glass (6W) | PAR20 | Med. Base | SW WG (2200K - 2700K) | 40° | 500 | 25000 | Y |  |
| 471219 | LED 50W Glass 3Pk (6W) | PAR20 | Med. Base | SW WG (2200K - 2700K) | 40° | 500 | 25000 | Y |  |
| 471185 | LED 50W Glass (6W) | PAR20 | Med. Base | BW (3000K) | 40° | 500 | 25000 | Y |  |
| 471227 | LED 50W Glass 3Pk (6W) | PAR20 | Med. Base | BW (3000K) | 40° | 500 | 25000 | Y |  |
| 471722 | LED 50W Glass 6Pk (6W) | PAR20 | Med. Base | BW (3000K) | 40° | 500 | 25000 | Y |  |
| 471193 | LED 50W Glass (6W) | PAR20 | Med. Base | DL (5000K) | 40° | 500 | 25000 | Y |  |
| 471235 | LED 50W Glass 3Pk (6W) | PAR20 | Med. Base | DL (5000K) | 40° | 500 | 25000 | Y |  |

T12

| | Part # | Description | Bulb Shape | Bulb Base | Colour (Temp.) | Lumens | Hours | Dim. | E-Star |
|---|--------|--------------|------------|------------|------------------|--------|-------|------|--------|
|  | 183947 | TL 15W | T12 18" | Med. Bipin | CW (4100K) | 695 | 9000 | N | |
|  | 248443 | TL 20W Plant | T12 24" | Med. Bipin | Plant (Plant) | 600 | 9000 | N | |
|  | 248492 | TL 20W | T12 24" | Med. Bipin | SW (3000K) | 1350 | 9000 | N | |
|  | 248690 | TL 20W | T12 24" | Med. Bipin | NTL (5000K) | 850 | 9000 | N | |
|  | 248740 | TL 20W 2Pk | T12 24" | Med. Bipin | DLX (6500K) | 1075 | 9000 | N | |
|  | 248948 | TL 20W 2Pk | T12 24" | Med. Bipin | CW (4100K) | 1200 | 9000 | N | |
|  | 273490 | TL 20W | T12 24" | Med. Bipin | SW (2700K) | 1250 | 9000 | N | |
|  | 248468 | TL 30W | T12 36" | Med. Bipin | SW (3000K) | 2400 | 24000 | N | |
|  | 248401 | TL 60W HO | T12 48" | R.D.C. | CW (4100K) | 4050 | 12000 | N | |
|  | 248450 | TL 40W Plant | T12 48" | Med. Bipin | Plant (Plant) | 1600 | 24000 | N | |