


Maestro Dual Controls Now with LED+ Technology

Expanded compatibility, same space-saving design

Features

- Stacked design—control two loads independently from a single location
- Advanced LED+ technology ensures compatibility with an extensive list of dimmable LED bulbs
- Easy installation—mounts in a standard, single-gang wallbox, no neutrals required
- MyLevel Personalization allows homeowners to customize dimmer settings
- · Works with high-efficiency bath fans





	MACL-L3S25-XX*	MACL-L3T251-XX
Description	LED+ dual dimmer and switch	LED+ dual dimmer and timer
Rating/load type	Dimmer: 75W LED, 300W Inc/Halogen Switch: 2.5A Lighting or Fan	Dimmer: 75 W LED, 300 W Inc/Halogen Timer: 2.5 A Lighting or Fan
Application	Single pole	Single pole
Neutral required	No	No
Timer Increments	N/A	5, 10, 15, 30, 45, 60, Always ON
Available Colors	Gloss: Almond (AL), Black (BL), Brown (BR), Gray (GR), Light Almond (LA), Ivory (IV), White (WH) Satin: Biscuit (BI), Mist (MI), Midnight (MN), Snow White (SW), Signal Red (SR), Taupe (TP)	Gloss: Almond (AL), Black (BL), Brown (BR), Gray (GR), Light Almond (LA), Ivory (IV), White (WH) Satin: Biscuit (BI), Mist (MI), Midnight (MN), Snow White (SW), Signal Red (SR), Taupe (TP)
List price	\$90 USD \$115 CAD	\$90 USD \$115 CAD



Dimmer and Switch



IVIACL-L3525-WF

Dimmer and Timer

