**PHILIPS** Lighting



# Core & Coil (71A) MH 175W - 450W

## CORE & COIL HID MH BAL 175W M57 120/277/347V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

#### **Product data**

General Information					
ANSI Code	M57-M107				
Lamp Type	175/150W MH				
Number of Lamps	1 piece/unit				
Circuit Type	CWA				
Ballast Type	Magnetic HID				
Base Model	71A55A0				
Core Size	3 X 4 (2 LW)				
Suitable For Outdoor Use	Yes				
Ignitor Catalog Number	NA				
Ignitor Temperature Rating	NA				
Capacitor Value	10 MFD				
Capacitor Catalog Number	7C100M40R				
Capacitor Requirements	400V				
Capacitor Temperature Rating	105°C				
Capacitor Diameter/Oval Dimensions	1.45 in				
Capacitor Height	3.75 in				
Automatic Restart	No				


Operating and Electrical					
Input Voltage	120/277/347 V				
Input Frequency	60 Hz				
Input Current (Open Circuit)	1.91/0.79/0.63 A				
Input Current (Starting)	0.94/0.41/0.33 A				
Input Current (Short Circuit)	0.78-1.17/0.35-0.52/0.25-0.32 A				
Secondary Short Circuit Current	1.51-1.85 A				
Constant Wattage Deviation	10%				
Ballast Factor (Nom)	1				
Power Factor (Nom)	0.90				
Open Circuit Voltage	305 V				
Input Current (Nom)	1.8/0.8/0.62 A A				
Input Power (Nom)	213 W				
Rated Lamp Power	175/150 W				
Wiring					
Wire Striplength	0.5 mm				
Wire Length by Color	12"				
Wire Type	Stranded				
Remote Wiring Configuration Allowed	Yes				

### Core & Coil (71A) MH 175W - 450W

Max Ballast-Lamp Distance Remote	Determined by AWG used				
Wiring					
Recommended Fuse Value	5/3/2 A				
Approval and Application					
Open Circuit Voltage Test (Volts)	275-337 V				
Approval Marks	ULR CSA certificate RoHS Compliant				
Temperature Marking	C/C/D				
UL Recognized	Yes				
Hipot Test (1 Minute)	2000 V				
Hipot Test (2 Seconds)	2500 V				
UL Insulation Class	H(180°C)				
UL Temperature Code	1029D				

Product Data	
Order product name	CORE & COIL HID MH BAL 175W M57
	120/277/347V KIT
EAN/UPC - Product	781087096543
Order code	913700525209
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700525209
Net Weight (Piece)	3.389 kg

#### **Dimensional drawing**



MH BAL 175W M57 120/277/347V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 175W M57	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
120/277/347V KIT						



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change