



# Core & Coil (71A) HPS ~LT~ 200W

## CORE & COIL HID HPS BAL 150W S55 120V C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	S55
Lamp Type	150W HPS
Number of Lamps	1 piece/unit
Circuit Type	R-NPF
Ballast Type	Magnetic HID
Base Model	71A8107B_NPF
Core Size	2 5/8 x 2 3/16
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	INTEGRAL
Ignitor Temperature Rating	125°C
Capacitor Value	NA
Capacitor Catalog Number	NA
Capacitor Requirements	NA
Capacitor Temperature Rating	NA
Automatic Restart	No
Operating and Electrical	
Input Voltage	120 V
Input Frequency	60 Hz
Input Current (Open Circuit)	0 A

Input Current (Starting)	4.5 A
Input Current (Short Circuit)	3.65-5.55 A
Secondary Short Circuit Current	3.65-5.55 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	120 V
Input Current (Nom)	3.2 A A
Input Power (Nom)	170 W
Rated Lamp Power	150 W

### Wiring

Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring 2'	
Recommended Fuse Value	15 A

### Approval and Application

Open Circuit Voltage Test (Volts)	114-126 V
-----------------------------------	-----------

## Core & Coil (71A) HPS ~LT~ 200W


Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

### Product Data

Order product name	CORE & COIL HID HPS BAL 150W S55 120V C&C
--------------------	---

EAN/UPC - Product	781087810774
Order code	913700501781
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	913700501781
Net Weight (Piece)	1.493 kg

### Dimensional drawing



HPS BAL 150W S55 120V C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 150W S55 120V C&C	3.60 in	2 in	2.6 in	2.2 in	2.2 in	1.8 in

