



FluxPanel Selectable LED (SBP)

2x4, wattage and CCT selectable backlit panel, 80 CRI, 35-45-50 watts and 3500K-4000K-5000K CCT

2x4, wattage and CCT selectable backlit panel, 80 CRI, 35-45-50 watts and 3500K-4000K-5000K CCT - 110 lm/W

The Selectable backlit panel is a highly versatile luminaire designed to provide three lumen and three CCT packages per size. Available for use in recessed, suspended, and surface mount applications, the SBP is a versatile luminaire that is ideal for general lighting applications such as open office, schools, healthcare, and retail.

Product data

General information		Enclosure	Metal and Plastic
Lamp Source Code	LED	Approval and application	
Colour Temperature	3500 4000 5000 K	Energy Certifications	DLC Standard
CRI	80	Initial performance (IEC compliant)	
Photometric Distribution Type	Diffuse	Luminaire Lumens	3000 3500 4000 lm
Mounting	T-Bar / T-Grid Surface	Efficacy	110 lm/W
Number Of Pieces	1	Product data	
Operating and electrical		Full product code	911401837881
Voltages	120-277 V	Order product name	2SBP3550L8CS-4-UNV-DIM
Luminaire Input Watts	33 37 47 W	EAN/UPC - Product	190096131013
Mechanical and housing		Order code	2SBP3550L8CS-4-UNV-DIM
Fixture Size	2 ft x 4 ft		

FluxPanel Selectable LED (SBP)

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	911401837881
Catalog Number	2SBP3550L8CS-4-UNV-DIM

Catalog Number Description	2x4, wattage and CCT selectable backlit panel, 80 CRI, 35-45-50 watts and 3500K-4000K-5000K CCT
-----------------------------------	---

