



## SlimSurface LED Downlight

SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 2700K CCT, 1000 lm,120V, Standard (TRIAC) dimming, wet location, Matte White Finish

SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 2700K CCT, 1000 lm,120V, Standard (TRIAC) dimming, wet location, Matte White Finish - 83.1 lm/W

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

## Product data

General information	
Lamp Source Code	LED
Colour Temperature	2700 K
CRI	80
Downlight Type	Open Downlight
Photometric Distribution Type	Direct
Mounting	Surface Wall
Fixture Finish	White
Number Of Pieces	1
Grade	Value Grade

Operating and electrical	
Voltages	120 V
Luminaire Input Watts	14 W
Conduit Connection	7/8 inch knockout
Mechanical and housing	
Fixture Size	6 in
Enclosure	Metal and Plastic
Approval and application	1
Energy Certifications	Energy Star

Datasheet, 2023, February 16 data subject to change

## SlimSurface LED Downlight

Initial performance (IEC compliant)		
Luminaire Lumens	900 lm	
Efficacy	83.1 lm/W	
Product data		
Order product name	SLIM 6" SQUARE 900 LM 27K 80CRI 120V WHT	
EAN/UPC - Product	662057988849	
Order code	S6S827K10	
Numerator - Quantity Per Pack	1	
Local code description	S6S827K10	

Numerator - Packs per outer box 1		
912401050028		
0.705 kg		
S6S827K10		
SlimSurface LED downlight, 6-inch square surface		
mount, 80 CRI, 2700K CCT, 1000 lm,120V, Standard		
(TRIAC) dimming, wet location, Matte White Finish		



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.