



SlimSurface LED Downlight

SlimSurface LED downlight, 4-inch square, surface mount, 80 CRI, 2700K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish

SlimSurface LED downlight, 4-inch square, surface mount, 80 CRI, 2700K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish - 67.6 lm/W

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

Product data

General information		Conduit Connection	
Lamp Source Code	LED	7/8 inch knockout	
Colour Temperature	2700 K	Mechanical and housing	
CRI	80	Fixture Size	4 in
Downlight Type	Open Downlight	Enclosure	Metal and Plastic
Photometric Distribution Type	Direct	Approval and application	
Mounting	Surface Wall	Energy Certifications	Energy Star
Fixture Finish	White	Initial performance (IEC compliant)	
Number Of Pieces	1	Luminaire Lumens	600 lm
Grade	Value Grade	Efficacy	67.6 lm/W
Operating and electrical			
Voltages	120 V		
Luminaire Input Watts	10 W		

SlimSurface LED Downlight

Product data

Order product name	SLIM 4" SQUARE 600 LM 27K 80CRI 120V WHT
EAN/UPC - Product	662057988788
Order code	S4S827K7
Numerator - Quantity Per Pack	1
Local code description	S4S827K7
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401050022

Net Weight (Piece)	0.419 kg
Catalog Number	S4S827K7
Catalog Number Description	SlimSurface LED downlight, 4-inch square, surface mount, 80 CRI, 2700K CCT, 650 lm,120V, Standard (TRIAC) dimming, wet location, Matte White Finish

