

Eaton UNL205 SA

Catalog Number: UNL205 SA

Eaton Crouse-Hinds series UNL union, Rigid/IMC, Copper-free aluminum, 3/4" to 3/4"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series UNL union	UNL205 SA
UPC	Product Length/Depth
782274164748	2.88 in
Product Height	Product Width
2 in	1.81 in
Product Weight	
0.24 lb	

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Conduit type

Rigid/IMC

Material

Copper-free aluminum

Trade size

3/4" to 3/4"

Resources

Catalogs

[Crouse-Hinds series Explosionproof Conduit Unions, Elbows and Tees catalog page](#)

Certification reports

[Explosionproof Conduit Unions, Elbows and Tees Canadian certification](#)

[Explosionproof Conduit Unions, Elbows and Tees UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - UNL205 SA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)