

# Eaton UNL105 SA

Catalog Number: UNL105 SA

Eaton Crouse-Hinds series UNL union, Rigid/IMC, Copper-free aluminum, 1/2"-1/2"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series UNL union	UNL105 SA
UPC	Product Length/Depth
782274449500	2.69 in
Product Height	Product Width
2 in	1.53 in
Product Weight	
0.19 lb	

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

## Product specifications

### Conduit type

Rigid/IMC

### Material

Copper-free aluminum

### Trade size

1/2"-1/2"

## Resources

### Catalogs

[Crouse-Hinds series Explosionproof Conduit Unions, Elbows and Tees catalog page](#)

### Certification reports

[Explosionproof Conduit Unions, Elbows and Tees Canadian certification](#)

[Explosionproof Conduit Unions, Elbows and Tees UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - UNL105 SA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)