

Electronic Timer Control - Intermatic Connect 365-Day Programmable Smart Wi-Fi Timer, 120-277 VAC, 3xSPDT, Indoor/Outdoor Plastic Enclosure

Item ETW3CP





## **PRODUCT DESCRIPTION**

The ETW Series offers 365 day scheduling, off-site access, and remote ON/OFF control through the easy-to-use Intermatic Connect app.

## **FEATURES**

- App based configuration and scheduling
- ► Up to 256 set points or events
- Up to 64 holiday blocks with schedule capabilities
- Automatic input voltage selection from 120 to 277 VAC, 50/60 Hz
- Local or remote connectivity
- Configurable outputs allow the control of various voltages and applications
- Relays incorporate zero-crossing technology to extend the life of the control
- ► Non-volatile EEPROM memory protects programming indefinitely
- ► LED compatible

## **APPLICATIONS**

- Indoor Lighting Control
- Outdoor Lighting Control
- ► Timing/Scheduling ON/OFF
- Machinery & Pump Controls

## **TECHNICAL DATA**

Control Specificatio

General	
Model Number	ETW3CP
Description	Intermatic Connect 365-Day Programmable Smart Wi-Fi Timer, 120-277 VAC, 3xSPDT, Indoor/Outdoor Plastic Enclosure
UPC Code	078275154025
Brand	Intermatic
Country of Origin (Intermatic)	THAILAND
Warranty Period	3-Year limited

Control Specifications	
Minimum ON/OFF Times	1 min
Maximum ON/OFF Times	Indefinite
Maximum ON/OFF Operations	256
Setpoint Program Count	256
ON/OFF Operations	256
Operation Features	Holiday
Operation Mode	365 day
Daylight Savings Adjustment	Automatic
Backup Type	Battery
Battery Type	CR2032 Lithium
Backup Protection Time	10 Years
Battery Service Type	Non-Serviceable
Minimum ON/OFF Operations	256
Minimum UN/OFF Operations	200



Application Compatibilities	Electronic Ballast; General Purpose; LED; Motor Load
Appication compatibilities	Lieutonic Ballast, General Fulpose, LED, Motor Loau
Mechanical Specifications	
Enclosure Type	Outdoor type 3
Dimensions	
Product Dimensions (H x W x D) in	7.5 x 8.875 x 3 in
Wire Size Min	#14 AWG
Wire Size Max	#8 AWG
Knockout Dimensions Bottom	(2) combination 1/2" - 3/4"
Knockout Dimensions Back	(1) combination 1/2" - 3/4"
Knockout Dimensions Left	(1) combination 1/2" - 3/4"
Knockout Dimensions Right	(1) combination 1/2" - 3/4"
Load Ratings	
General Purpose (NC) Range(s)	10 A
General Purpose (NO) Range(s)	30 A
Motor Load Ratings Ranges	1 HP, 120 VAC; 2 HP, 240 VAC; LRA: 96 A, 120 VAC; 90 A, 240 VAC
Motor Load Ratings NO Ranges	1 HP, 120 VAC; 2 HP, 240 VAC
Electronic Ballast LED	16 A
Electrical Specifications	
Voltage Selection Type	Auto Voltage
Wiring Option	Terminals
Input Voltage Range(s)	120-277 VAC, 50/60 Hz
Number of Circuits	3
Switch Type	SPDT
Maximum Power Consumption (W)	7 W
Packaging	
Shipping Weight (lbs)	2.39
Unit Carton Dimensions (H x W x L) in	4.375 x 9.5 x 10 in
Product Weight (kg)	1.084
Product Weight (lbs)	2.39
Environmental Specifications	
Temperature (operation)	-40 °F to 158 °F / (-40 °C to 70 °C)
Standards and Certifications	
UL Certification	cULus
Other Certifications and Compatibilities	FCC; LED
California Proposition 65	Nickel
RoHS Certification	Yes