

Project:		Type:
Drawn by:	Catalogue #:	Date:

Individual Spec Sheet

CIRKA

LED CEILING LUMINAIRE

9"

ORDERING INFORMATION

68057 Order code: CRK-9-40-1 Model number: UPC: 069549013841

Case quantity: ES unique ID: 2358093

PHYSICAL DATA

Dimensions in (mm): 8 7/16" (225.6) Lens Finish: Frosted

Housing Finish: White With An Anti-Corrosive Paint Finish Mounting: Surface - Wall And Ceiling Mount

PERFORMANCE DATA

Watts (W): 18 Volts (VAC): 120 Color temperature (K)1: 4 000 Lumen output (lm)2: 1 300 Efficiency (Im/W): 72 CRI: 80+ Life L70 (h)3: 50 000 Dimming: Yes Power factor: >0.9 THD (%): <40 Frequency (Hz):

Operating temp. range: -20°C to 40°C (-4°F to 104°F)

COMPATIBLE DIMMERS

Brand	Model
LEVITON	6672-1LW; IPL06-10Z; DSL06-1LZ; 6674-P0W
LUTRON	DVW-603PGH-WH; MACL-153MR-WH; SCL-153P-WH; PD-6WCL-WH; CTCL-153P-WH; MSCL-0P153M-WH; DVCL-153P-WH
GE	45857GR

NOTE: The above table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Stanpor recommends to use dimmers designed for inachidescent products during the system of the construction of the construction

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.















damp location













¹ Typical color temperature range: +/- 5 %

² Lumen values are derived from Energy Star.

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.



CIRKA LED CEILING LUMINAIRE - 68057


COMPATIBLE ACCESSORIES

Order code	Model number	(master)
RNG-TRM09-BN	9" Brushed Nickel Trim	20
68901	9" Polished Black Trim	20
68902	9" Polished Chrome Trim	20
RNG-TRM09-BRG	9" Brushed Rose Gold Trim	20
RNG-TRM09-BB	9" Brushed Bronze Trim	20

SCREWLESS MAGNETIC TRIMS




DIMENSIONS



PHOTOMETRIC DATA¹

68057 • CRK-9-40-1 • 1 470.1 lm

Polar candela distribution



Zonal lumen summary


Zone	Lumens	% Fixture		
0-30	410.9	28		
0-40	671.8	45.7		
0-60	1 180.7	80.3		
60-90	289.3	19.7		
0-90	1 470.1	100		

Illuminance at a distance

Center beam fc		Beam width			
1.7'	184			4.9'	4.9'
3.3'	49.0			9.6'	9.5'
5.0'	21.3			14.5'	14.4'
6.7'	11.9			19.4'	19.3'
8.3'	7.74	_		24.0'	24.0'
10.0'	5.33			28.9'	28.9'
	Vert. spread:	110.7°	Hor. spread	: 110.6°	

Qty		Description	Price	
accept the specifications of the luminaire configuration mentioned above. Name:				
Company: Signature:				
Signature:			Date:	

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.



¹ Complete IES files available on our website.