

Eaton 10250T30B-POP

Catalog Number: 10250T30B-POP

10250T, 30.5 mm, Heavy-Duty, Standard, square, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Momentary, Black actuator, Black field, START and JOG (two plates), Flush, 1NO-1NC, Chrome bezel, Plastic actuator

General specifications



Product Name

Eaton 10250T pushbutton

UPC

782114408469

Product Height

3 in

Product Weight

0.43 lb

Compliances

CE Marked

Catalog Notes

Point of Purchase Package

Catalog Number

10250T30B-POP

Product Length/Depth

7 in

Product Width

6 in

Warranty

1 year

Certifications

UL Listed

CSA Certified



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

30.5 mm, Heavy-Duty

Actuator color

Black

Bezel

Chrome

Legend

START and JOG (two plates)

Mounting

Flush

Actuator material

Plastic

Field color

Black

Illumination

Non-illuminated

Operating mode

Momentary

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Series

10250T

Size

Standard, square

Contact configuration

1 NO-1 NC

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Quick Selector - 10250T Pilot Devices

Eaton Specification Sheet - 10250T30B-POP



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)