

Eaton 10250T476C21-1-POP

Catalog Number: 10250T476C21-1-POP

Eaton 10250T, 30.5 mm, Heavy-Duty, Standard, square, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Mom., Extended, Red actuator, Black field, POWER ON, Incandescent, FV light unit, 1NO-1NC, 24 Vac/dc LUV, Chrome bezel, 24 Vac/dc lamp

General specifications



Product Name

Eaton 10250T pushbutton

Catalog Number

10250T476C21-1-POP

UPC

782114408551

Product Length/Depth

6.4 in

Product Height

2.5 in

Product Width

5.5 in

Product Weight

0.43 lb

Warranty

1 year

Compliances

CE Marked

Certifications

CSA Certified

UL Listed

Catalog Notes

Includes 2 extra lenses: Green and Amber

defaultTaxonomyAttributeLabel

Type

30.5 mm, Heavy-Duty

Actuator color

Red

Bezel

Chrome

Lamp voltage

24 Vac/dc

Legend

POWER ON

Actuator material

Plastic

Actuator

Extended

Field color

Black

Illumination

Illuminated

Light unit type

Incandescent, full voltage

Light unit voltage

24 Vac/dc

Operating mode

Momentary

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Series

10250T

Size

Standard, square

Contact configuration

1 NO-1 NC

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T476C21-1-POP

Quick Selector - 10250T Pilot Devices



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)