

Eaton 10250T21KB

Catalog Number: 10250T21KB

Eaton 10250T pushbutton, Assembled selector switch, 10250T, 30.5 mm, Heavy-Duty, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Knob, Black actuator, 2NO



General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T21KB
UPC	Product Length/Depth
782113358307	3.56 in
Product Height	Product Width
1.77 in	2.03 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Type

30.5 mm, Heavy-Duty

Actuator color

Black

Actuator

Knob

Contact configuration

2 NO

Illumination

Non-illuminated

NEMA rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Series

10250T

Number of positions

3

Throw type

60 °

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T21KB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)