

Eaton C25HNE3120A

Catalog Number: C25HNE3120A

Eaton definite purpose contactor, Non-reversing contactors and starters (C306) ,120A, two- and three-pole ,Open with metal mounting plate ,Box lugs (posidrive setscrew) , 110–120 Vac, 50/60 Hz



General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25HNE3120A
UPC	Product Length/Depth
782114182413	5.94 in
Product Height	Product Width
7.17 in	3.54 in
Product Weight	Warranty
8.7 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified
Catalog Notes	
Resistive Load rating per pole	

defaultTaxonomyAttributeLabel

Amperage Rating

120A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

110-120 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

120 A

Model

Contactor

Resistive load

140 A

Size

120 A, two-pole and three-pole

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25HNE3 AutoCAD 2D Footprint](#)

[C25HNE3 3D Inventor](#)

[C25HNE3 2D PDF](#)

[C25HNE3 2D Drawing Xchange](#)

[C25HNE3AutoCAD 2D Footprint \(mm\)](#)

[C25HNE3 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - C25HNE3120A](#)