

Eaton C25DND330B-GL

Catalog Number: C25DND330B-GL

Eaton definite purpose contactor, Quick, 30A, 208-240 Vac at 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, Contactor, Three-pole, Global ratings, Screw/pressure plate and quick connect terminals (side-by-side)

General specifications



Product Name

Eaton definite purpose contactor

Catalog Number

C25DND330B-GL

UPC

786685627625

Product Length/Depth

3.35 in

Product Height

2.5 in

Product Width

2.4 in

Product Weight

1.3 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked
RoHS Compliant

Certifications

CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Three-pole

Special features

Global ratings

Coil voltage

208-240 Vac, 50-60 Hz

Enclosure

Open with metal mounting plate

Frame

15-50 A, two-pole or three-pole

Frame size

15-50 A, two-pole and three-pole

Model

Contactor

Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25DND3 3D Model Xchange](#)

[C25DND3 3D Inventor](#)

[C25DND3 AutoCAD 2D Footprint](#)

[C25DND3 AutoCAD 2D Footprint \(mm\)](#)

[C25DND3 2D Drawing Xchange](#)

[C25DND3 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - C25DND330B-GL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)