

48-39-0631


### 30-9/16 in. 12/14 TPI COMPACT EXTREME THIN METAL BAND SAW BLADE 3PK

★★☆☆ 1.8 (12) Write a review

The MILWAUKEE® Extreme Metal Band Saw Blades maximize your band saw blade performance. These blades deliver what you need for daily job site use - more cuts and fewer blade changes. An aggressive variable tooth design gives you the versatility to cut more metals of various thicknesses without changing blades. Our band saw blade sizes are also available in deep cut (44 7/8"), compact (35 3/8"), compact (30-9/16") and sub-compact (27").

#### INCLUDES

(1) 30-9/16 in. 12/14 TPI COMPACT EXTREME THIN METAL BAND SAW BLADE 3PK (48-39-0631)



#### KEY FEATURES

#### SPECIFICATIONS

#### REVIEWS

- ✓ More Cuts. Less Blade Changes.
- ✓ 2X Faster in Thin Metals
- ✓ Variable TPI for Versatility in All Metal Thickness
- ✓ Made in the USA with global materials
- ✓ 3X Life in Stainless Steel and other extreme metals.
- ✓ 25% More Cuts Per Charge
- ✓ Optimized Tooth Design for clean cuts
- ✓ Fits M12 FUEL COMPACT BAND SAW (2529-20/21XC)

#### PRODUCT SPECIFICATIONS

Number of Teeth	Display=382&Actual=382
TPI	12/14
Blade Length	30.5625 in
Pack Qty	3
Size	30 9/16
Length	15.3 in

Weight	0.321 lb
Height	0.85 in
Width	7.05 in
Material Thickness	Thin Metal
Material Application	Medium Metal