

Eaton BR280

Catalog Number: BR280

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 80 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #8-1/0 AWG Cu/Al, Q28, BR, Type BR Loadcenters

General specifications



Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR280
	UPC
	786676363174
Product Length/Depth	Product Height
1.9 in	2.5 in
Product Width	Product Weight
2.9 in	0.6 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

80 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#8-1/0 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR280](#)