






















LUNA™ DESIGNER SERIES 2"

The all new WET location rated LUNA 2", provides a small aperture with a powerful output, offering up to 560 lumens and 90+ CRI along with a CCT Selectable switch for 27-50K color temperatures. Perfect for remodel or new construction in residential applications and wall niches in small commercial spaces.

FEATURES:

- IC Rated
- WET location rated
- Energy Star
- JA8-2016, TITLE 24
- Lifetime warranty
- CCT Select 5 position (27-50K)
- Remodel
- Up to 560 lumens
- 90+ CRI
- DIM TO WARM
- Dimmable
- LUNA is also available in 3", 3.5",
 4" and 5" or 6" for project uniformity



CCT Select Switch

COLOR OPTIONS

WHITE (WH)



BLACK (BK)



BRUSHED NICKEL (BN)





ACCESSORIES



NEW CONSTRUCTION MOUNTING KIT (A+B) PRE-MOUNTING PLATE (A) HANGER BARS (B)



BUTTERFLY BRACKETS (C) PRE-MOUNTING PLATE (A)



60" FLEXIBLE CONNECTOR
TO EXTEND THE DISTANCE
BETWEEN THE FIXTURE
AND DRIVER



VAPOR BARRIER



COMMERCIAL GRADE DRIVER 120~347V / 120~277V, 0-10V DIMMING

ORDERING GUIDE		SIZE	WATTS	COLOR TEMP.	CRI	TRIM FINISH
2" FIXED	ROUND: SQUARE:	RA2 RA2S	- 7F - - 7F -	Leave blank for CCT Select - 5 position (27-50K) DTW : DIM TO WARM	- 90 - 90	WH:WHITE BK: BLACK BN: B.NICKEL

Liteline Corporation Copyright © 2019 All rights reserved. Telephone 416.996.1856 1.866.730.7704 Fax 905.709.5255 1.888.738.9736

LITELINE.COM/LUNA



M-LUNA2-E REV 05.31.19