

Eaton BR120

Catalog Number: BR120

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240V, BR, #14-4 AWG Cu/Al, Q1, BR, Type BR loadcenters



General specifications

| | |
|---|--|
| Product Name | Catalog Number |
| Eaton BR thermal magnetic circuit breaker | BR120 |
| | UPC |
| | 786676362108 |
| Product Length/Depth | Product Height |
| 2.5 in | 3 in |
| Product Width | Product Weight |
| 1 in | 0.3 lb |
| Warranty | Compliances |
| Limited lifetime residential, 1 year commercial | Federal Specifications Classification W-C375 |
| Certifications | |
| UL 489 | |

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

20 A

Voltage rating

120/240 V

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Single-pole

Quantity

1

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Type BR, BD, BQ, BQC,BRH, GFCB, GFCBH, 10-70Amp 1-Pole - Curve](#)

Specifications and datasheets

[Eaton Specification Sheet - BR120](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)