

Eaton C25DNJ250A

Catalog Number: C25DNJ250A

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (vertical in-line), 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, Contactor, Two-pole, Box lugs (posidrive setscrew), Non-reversing

General specifications



Product Name

Eaton definite purpose contactor

Catalog Number

C25DNJ250A

UPC

782116300457

Product Length/Depth

3.35 in

Product Height

3.75 in

Product Width

2.4 in

Product Weight

1.3 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

RoHS Compliant
CE Marked

Certifications

UL Listed file E1491 (Guide Number NLDX2)
CSA Certified

defaultTaxonomyAttributeLabel

Accessories

Mounting plate

Number Of Poles

Two-pole

Type

Non-reversing

Auxiliary contacts

Quick connect (vertical in-line)

Coil voltage

110-120 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Model

Contactor

Series

E1

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

C25DNJ2 2D PDF

C25DNJ2 AutoCAD 2D Footprint (mm)

C25DNJ2 3D Model Xchange

C25DNJ2 AutoCAD 2D Footprint

C25DNJ2 3D Inventor

C25DNJ2 2D Drawing Xchange

Specifications and datasheets

Eaton Specification Sheet - C25DNJ250A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia