



LED Filament High Intensity



ED23.5 20W 120-277 V

ED28 40W 120-277 V

ED37 65W 120-277 V

Order code	Description	Watts (W)	Base	Volts (VAC)	Color temp. (K)	CRI	Beam angle (°)	Life L70 (hrs)	Lumen output (lm)	Case qty (master)
69598	ED23.5/20W/40K/BYP/EX39/V/FIL/ND/STD	20	EX39	120-277	4 000	80	Universal	25 000	3 500	12
69599	ED28/40W/40K/BYP/EX39/V/FIL/ND/STD	40	EX39	120-277	4 000	80	Universal	25 000	7 500	12
69600	ED37/65W/40K/BYP/EX39/V/FIL/ND/STD	65	EX39	120-277	4 000	80	Universal	25 000	12 000	6

Traditional Equivalent

LED	CFL	Incandescent	HID
20 W	65W	200W	75W
40 W	105W	400W	250W
65 W	150W	750W	400W

Lumen values are derived from photometric testing

