

# Eaton C25FNF375A

Catalog Number: C25FNF375A

Eaton definite purpose contactor, 60–75A, two- and three-pole ,Open with metal mounting plate ,Box lugs (posidrive setscrew) and quick connect terminals (side-by-side) ,110–120 Vac, 50/60 Hz



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C25FNF375A
<b>UPC</b>	<b>Product Length/Depth</b>
782114117453	3.97 in
<b>Product Height</b>	<b>Product Width</b>
3.75 in	2.63 in
<b>Product Weight</b>	<b>Warranty</b>
2.66 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	CSA Certified
	UL Recognized

## Catalog Notes

Resistive Load rating per pole

**Amperage Rating**

75A

**Number Of Poles**

Three-pole

**Type**

Non-reversing

**Coil**

110-120 Vac, 50/60 Hz

**Contact configuration**

1 NO, 1 NC

**Enclosure**

Open with metal mounting plate

**Frame size**

15-50 A, two-pole and three-pole

**Inductive full load**

75 A

**Model**

Contactor

**Resistive load**

90 A

**Terminals**

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

**Connection**

Quick

**Catalogs**[Eaton's Volume 5—Motor Control and Protection](#)**Drawings**[C25FNF3 3D Inventor](#)[C25FNF3 AutoCAD 2D Footprint \(mm\)](#)[C25FNF3 2D PDF](#)[C25FNF3 3D Model Xchange](#)[C25FNF3 AutoCAD 2D Footprint](#)**Specifications and datasheets**[Eaton Specification Sheet - C25FNF375A](#)