

Eaton AN16DN0AB

Catalog Number: AN16DN0AB

Eaton Freedom NEMA motor control starter, Non-Reversing Reset Overload Relay Starter, 2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V maximum horsepower, 120V/60 Hz or 110V/50 Hz coil voltage, 27A, Three-pole, Size 1



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN16DN0AB
	UPC
	782113971704
Product Length/Depth	Product Height
4.61 in	3.31 in
Product Width	Product Weight
4.38 in	2.6 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	Catalog Notes
	Heater Packs must be purchased separately

defaultTaxonomyAttributeLabel

Special features

Starter w/C306 bi-metal OLR

HP rating - max

2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V

Phase

Single-phase, three-phase

Amperage Rating

27A

Size

1

Mounting

Horizontal

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[AN16DN0_B 2D Drawing Xchange](#)

[AN16DN0_B 2D PDF](#)

[AN16DN0_B AutoCAD 2D Footprint](#)

[AN16DN0_B 3D Model Xchange](#)

[AN16DN0_B AutoCAD 2D Footprint \(mm\)](#)

[AN16DN0_B 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - AN16DN0AB](#)

[Quick Selector - NEMA Contactors](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia