

Eaton E50RA

Catalog Number: E50RA

Eaton E50 NEMA heavy duty plug-in limit switch receptacle, Gravity return, Screw Terminals, Rear or front mounting, Single-pole



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch receptacle	E50RA
	UPC 782113290720
Product Length/Depth	Product Height
2.92 in	1.06 in
Product Width	Product Weight
1.54 in	0.11 lb
Warranty	Certifications
1 year	UL Recognized CSA Certified

Number Of Poles

Single-pole

Enclosure material

Die cast zinc

Connection

Screw terminal

Operating temperature - max

250 °F

Operating temperature - min

-40 °F

Series

E50 heavy duty plug in

Switch type

Gravity return

Environmental ratingNEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67**Mounting method**

Front

Rear

Catalogs[Eaton's Volume 8—Sensing Solutions](#)**Specifications and datasheets**[Eaton Specification Sheet - E50RA](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)