Excel

When looking for a modern design, a square lighting fixture is often the best choice. Even better, imagine being able to use a round cutout for installation. This is now a reality with the improved concept of this square panel light.























Model	Size	Watts	Delivered lumens	CRI	Color °T	Standard voltage	Multi-voltage 🖣
5004-DW*	4"	11 W	850 lm	80	3000 K - 2200 K	120 V, Triac dimming	MV: 120 / 277 / 347V, 0-10V dimming
5004-FR-CC**	4"	11 W	825 lm		2700, 3000, 3500, 4000, 5000 K		
5006-FR-CC**	4"	14 W	1230 lm	.000,0000			

^{*}Dim-to-warm technology dims from 3000 K to 2200 K

Specifications

Every fixture includes a junction box with an integrated driver

Over 35,000 hours of service life

Can be daisy chained

Superior LED performance and lifespan

Smooth 360° wide spread

Minimal heat emission

Frosted lens

Edge lit technology

Aluminum construction

Switch-selectable CCT: 2700 K/3000 K/

3500 K/4000 K/5000 K

Very low profile

IC certification (suitable for direct contact with insulation)

Air-tight certified as per ASTM E283-04

Suitable for wet locations

Refer to website for dimmer compatibility

Ideal operating temperature:

-20° to 40° C

4-1/8" x 2-1/2"

x 1-3/8"

5-year warranty

Finish



BK Black

Accessories

REC-TRIM4-BK (5004-DW only)

4" recessed panel trim in black

REC-TRIM4-GD (5004-DW only)

4" recessed panel trim in gold

REC-TRIM4-SN (5004-DW only)

4" recessed panel trim in satin nickel

REC-3K-EXT8FT (5004-DW only)

8-foot extension cable

REC-3K-EXT20FT (5004-DW only)

20-foot extension cable

REC-CC-EXT8FT (5004/6-FR only)

8-foot extension cable

REC-CC-EXT20FT (5004/6-FR only)

20-foot extension cable

RFP-46 (5004, 5006)

Rough-in plate

5004-FR

 $\times 1-3/8$ "

RFP-UNI (5004, 5006)


Universal rough-in plate

Multi-voltage 🧗


This product family offers multi-voltage drivers (120/277/347) that are dimmable using 0-10V dimming systems. Please note that longer lead times may apply for this option. Kindly reach out to your DALS representative for additional information and to confirm availability.

Note


Other color temperatures, finishes, and voltage options are available but may require minimum order quantities (MOQs) and longer lead times. Please contact your DALS representative for more information.



Ø4-3/4"



Ø4-1/4"



^{**2-}hour fire-rated without additional housing or hardware, in accordance with UL 263, ASTM E119, and CAN ULC S101