



21-01



*designed especially with breakaway base to prevent vehicle/pedestal damage*

Model #1A-DPP-1 shown complete with Model #DR45-1 Handy Hood

## DELUXE VEHICLE POWER PEDESTAL Model #1A-DPP

- EEMAC 3R enclosure
- Specifically designed for superior appearance. Durable, long lasting, corrosion resistant, galvanized metal construction prevents rusting and assures long lasting quality finish
- Base is constructed with galvanized steel with breakaway capabilities
- Mounting bolts are turned in to prevent personal injury (no outward base flange, no visible base plate = no rust)
- 24”H x 7”W x 6”D pedestal body and front access cover
- Safety soft, machine formed corners on hood with smooth edges for ultimate safety and soft European appearance
- Cross-brake style roof
- ASA 61 grey powder coat finish
- Leviton #5320 duplex receptacle complete with weatherproof cover
- Devices and covers supplied loose for field installation
- CSA certified pedestal
- 3/8” Mounting fasteners not included - suggested is Hilti style

### Options

- Model #DR45-1 Handy Hood complete with weatherproof cover
- While-in-use receptacle cover
- 15/20A #5-20R duplex receptacle  • GFCI

Model #	Receptacles	
	Qty.	Description
1A-DPP-1	1	15A Duplex Receptacle
1A-DPP-2	2	15A Duplex Receptacles
1A-DPP-3	3	15A Duplex Receptacles
1A-DPP-4	4	15A Duplex Receptacles