

---

# Echo

Inspiration will come in abundance once you try our LED accent step lights. Use them outdoors on your deck or on the stairs inside your home. You will be truly impressed by the effect!



Model	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
<b>LEDSTEP002D</b>	3 W	70 lm	285 lm	80	3000 K	120 V

**Specifications**

Die-cast aluminum housing  
 Over 50,000 hours of service life  
 Warm white light output  
 Optimized light spread  
 Low power consumption  
 Excellent color rendering  
 Superior light color consistency  
 Aesthetic profile  
 Dimmable  
 Install in standard electrical junction box  
 Suitable for wet locations  
 Refer to website for dimmer compatibility  
 Ideal operating temperature:  
 -20° to 40° C  
 5-year warranty

**Finish**

- **BK** Black
- **SG** Silver grey
- **WH** White

**Note**

Other color °T and finishes available, but may require MOQ's and longer lead times. Please contact your DALs representative for more information.



**LEDSTEP002D**

