

Threaded products and hardware

E142 Hex head cap screw

Std. pack 100




Cat. no.	Size (in.)	Wt./C lb
E142-1/4x100EG	¼ x 1	1.74
E142-1/4x150EG	¼ x 1½	2.43
E142-3/8x100EG	⅜ x 1	4.17
E142-3/8x150EG	⅜ x 1½	5.64
E142-1/2x100EG	½ x 1	8.94
E142-1/2x150EG	½ x 1½	10.00
E142-1/2x200EG	½ x 2	11.19
E142-1/2x225EG	½ x 2¼	11.90
E142-1/2x250EG	½ x 2½	12.52
E142-1/2x275EG	½ x 2¾	13.22

Available in stainless steel.

E150S Lag bolt

Std. pack 50



Cat. no.	Drill size (in.)	Size (in.)	Wt./C lb
E150S-3/8x1-1/2EG	¼	⅜ x 1½	5
E150S-3/8x2EG	¼	⅜ x 2	7
E150S-3/8x2-1/2EG	¼	⅜ x 2½	8
E150S-3/8x3EG	¼	⅜ x 3	9
E150S-1/2x1-1/2EG	11/32	½ x 1½	12
E150S-1/2x2EG	11/32	½ x 2	13
E150S-1/2x2-1/2EG	11/32	½ x 2½	15
E150S-1/2x3EG	11/32	½ x 3	18


H104 Hanger rod continuous threaded

Std. pack 3

- Black available upon request
- Sold per foot; standard length, 10 ft.
- Also available in stainless steel (316) standard length 6 ft. (suffix SS6)
- National coarse thread

Cat. no.	Thread size (in.)	Wt./lb 100 ft.	Design Load lb
H104-1/4x10EGC	¼	12.5	150
H104-3/8x10EGC	⅜	29	610
H104-1/2x10EGC	½	53.5	1,130
H104-5/8x10EGC	⅝	85	1,810
H104-3/4x10EGC	¾	123	2,710
H104-7/8x10EG	7/8	130	3,770
H104-1x10EG	1	214	4,960

H119 Rod couplings – standard

Diagram	Rod size	A (in.)	Wt./C lb
	¼	7/8	1.90
	5/16	7/8	3.75
	⅜	1⅛	3.50
	½	1¼	5.50
	⅝	2⅛	18.00
	¾	2¼	28.00
	7/8	2½	55.00
	1	2¾	56.00

Standard rod coupling

Example: H119-1/2EG

Order by product number, rod size, and finish.

Available in stainless steel.

H119 Rod couplings – reducing

Rod size	A (in.)	Wt./C lb
¼ to ⅜	1½	3.50
⅜ to ½	1¼	6.70
½ to ⅝	1¼	14.00
⅝ to ¾	1½	21.00
¾ to 7/8	1¾	40.00

Rod reducer coupling

Example: H119-1/4x3/8EG