

Eaton ECSNOASC

Catalog Number: ECSNOASC

Eaton CurrentWatch ECS Top Terminal Current Switch, Adjustable 1-150A setpoint, LED indicator, Screw Terminals, 0.15A at 240 Vac/dc, Solid-Core housing, SSR, Self powered

General specifications



Product Name	Catalog Number
Eaton ECS series CurrentWatch AC current switch	ECSNOASC
	UPC
	786685120911
Product Length/Depth	Product Height
3.5 in	2.18 in
Product Width	Product Weight
0.93 in	0.33 lb
Warranty	Compliances
1 year	RoHS Compliant

defaultTaxonomyAttributeLabel

Contact Rating

0.15A at 240 Vac/dc

Operating Temperature

-58° to 122°F

Enclosure

Solid-core housing

AC current - max

150 A

Contact configuration

SSR

Enclosure material

UL94 V0 flammability rated plastic

Input voltage

Self powered

LED indicator

LED indicator

Switch type

Adjustable 1-150 A setpoint

Connection

Screw terminal

Resources

Brochures

[CurrentWatch current sensors](#)

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - ECSNOASC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)