

Eaton ECSNOASP

Catalog Number: ECSNOASP

Eaton CurrentWatch ECS Top Terminal Current Switch, Adjustable 1.75-150A setpoint, LED indicator, Screw Terminals, 0.15A at 240 Vac/dc, SSR, Self powered

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton ECS series CurrentWatch AC current switch | ECSNOASP |
| | UPC |
| | 786685120935 |
| Product Length/Depth | Product Height |
| 3.53 in | 2.25 in |
| Product Width | Product Weight |
| 1.19 in | 0.33 lb |
| Warranty | Compliances |
| 1 year | RoHS Compliant |

defaultTaxonomyAttributeLabel

Contact Rating

0.15A at 240 Vac/dc

Operating Temperature

-58° to 122°F

AC current - max

150 A

Contact configuration

SSR

Enclosure material

UL94 V0 flammability rated plastic

Input voltage

Self powered

LED indicator

LED indicator

Switch type

Adjustable 1.75-150 A setpoint

Connection

Screw terminal

Resources

Brochures

[CurrentWatch current sensors](#)

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - ECSNOASP](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia