

Eaton EGK3125KSG

Catalog Number: EGK3125KSG

Eaton Series G molded case switch, EG-frame, EG, Molded case switch, Three-pole, 125A, 600Y/347 Vac, Line and load, Metric



Photo is representative

General specifications

Product Name

Eaton Series G molded case switch

Catalog Number

EGK3125KSG

UPC

782113960708

Product Length/Depth

3.38 in

Product Height

6 in

Product Width

4.13 in

Product Weight

4.5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked

Certifications

UL Listed
IEC Rated
CSA Certified

Catalog Notes

Molded case switches may open above 1250A

defaultTaxonomyAttributeLabel

Type

Molded case switch

Amperage Rating

125 A

Voltage rating

600Y/347 Vac

Circuit breaker type

EG

Circuit breaker frame type

Molded case switch

Series

Series G

Terminals

Line and load

Frame

EG

Mounting hardware

Metric

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Multi-wire lugs product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[StrandAble terminals product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Motor protection circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[Series G MCCB quick selector](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[EG-frame Molded Case Circuit Breaker Drawing](#)

Specifications and datasheets

[Eaton Specification Sheet - EGK3125KSG](#)

[MOEM MCCB product selection guide](#)

[EG-Frame Circuit Breaker 15-160 Amperes Technical Data](#)

[NG and ND-Frame molded case circuit breakers](#)

Time/current curves

[Eaton Series G type EGB, EGE, EGS, EGH, EGC, and EGK circuit breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)