

Eaton EGFL1NCLAT3

Catalog Number: EGFL1NCLAT3

Eaton CurrentWatch Series Ground Fault Sensor, Current Switch, UL94 V0 Flammability Rated Plastic enclosure, 1A max AC, 2A max DC, SPST Latching Mechanical Relay, 1A at 125Vac / 2A at 30Vdc, Screw Terminals, 120 Vac input

General specifications



Product Name	Catalog Number
Eaton EGF series CurrentWatch ground fault sensor	EGFL1NCLAT3
	UPC
	786685223681
Product Length/Depth	Product Height
3.25 in	4.2 in
Product Width	Product Weight
2.99 in	0.25 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL/CUL listed	

defaultTaxonomyAttributeLabel

Contact Rating

1A at 125Vac / 2A at 30Vdc

Operating Temperature

-4° to 122°F (-20° to 50°C)

AC current - max

1 A

Contact configuration

SPST latching mechanical relay

Enclosure material

UL94 V0 flammability rated plastic

Input voltage

120 Vac

LED indicator

Power on: green LED, contact status: red LED

Switch type

Current switch

Connection

Screw terminal

Resources

Brochures

[CurrentWatch current sensors](#)

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - EGFL1NCLAT3](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)