

Eaton ECX09C5ABA

Catalog Number: ECX09C5ABA

Eaton XT IEC electronic motor starter, 120 V, NEMA 4X, Non-combination, 9 A, START/STOP pushbutton, Non-reversing, 0.16-0.25 FLA



General specifications

Product Name	Catalog Number
Eaton XT IEC electronic motor starter	ECX09C5ABA
UPC	Product Length/Depth
786685540726	6.7 in
Product Height	Product Width
13.31 in	9.84 in
Product Weight	Warranty
295 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
CSA Certified UL Listed IEC Rated	Non-Combination Ampere Rating. See Tab 1 for enclosure type/IP rating cross-reference. No disconnect.

Coil voltage

120 V

Enclosure

NEMA 4X

Type

Non-combination

Amperage Rating

9A

Actuator

START/STOP pushbutton

Operation

Non-reversing

Overload relay

0.16-0.25 FLA

Brochures

[ECX Non-metallic Starters To 25 HP](#)

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECX09C5ABA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)