



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Part Number	Width in. (mm)	Length ft. (m)	Thickness in. (mm)	Package per Roll	Description	Insulation Color	Weight oz. (gram)
ST15-075-66GRYL	.75 (19)	66(20)	.005(.13)	CELLO WRAP	GENERAL PURPOSE ST15 GREEN/YELLOW, .75"x66'x.005"	GREEN/YELLOW	2.3 (64)

TAPE
WIDTH
±0.08
±[2.0]



TAPE
THICKNESS
±0.002
±[0.05]



NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- MATERIAL: RUBBER ADHESIVE PRESSURE SENSITIVE VINYL TAPE.
- SUITABLE FOR USES UNDER 600 V OR 80 °C (176°F)
- MEETS UL-510A.
- COMPLIANT TO CALIFORNIA PROP. 65
- THE LENGTH TOLERANCE IS +1.3 FT (0.4 M), -0.3 FT (0.1 M).



PART NUMBER ST15-075-66GRYL		TITLE Stronghold Insulating Tape-General Purpose ST15 Tape	
ITEM REVISION NAME 00351EBT/00		CUSTOMER DRAWING	
DATASET FILE NAME 00351EBT_DC/00B		PANDUIT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			
.x ± .1 [2.54] .xxx ± .005 [.127]		MATERIAL: SEE NOTE3	
.xx ± .01 [.25] ANGLES ± 1°		DRAWING NUMBER: 00351EBT_DC	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY JSUN	DATE 4/29/2019	CHK ADAH	SCALE NONE
REV		SIZE A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00B	02-23-24	BDK	JADE	DJSL	A. REMOVED NOTE "5. FLAME RETARDANT." AND RENUMBERED NOTES	046173 r01
00	4/29/2019	JSUN	ADAH	JHAC	INITIAL RELEASE	046173/00

ANGLOBAL_ASIZE