

# Eaton M22-LEDC-W

Catalog Number: M22-LEDC-W

Eaton M22 modular pushbutton, LED Light Unit, Base, Screw, IP66, NEMA 4X, 13, Rk resistance 100, Illuminated, White, 12-30 Vac/dc



## General specifications

### Product Name

Eaton M22 modular pushbutton

### Catalog Number

M22-LEDC-W

### UPC

786685277684

### Product Length/Depth

2 in

### Product Height

1 in

### Product Width

2 in

### Product Weight

0.1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

Bureau Veritas  
CE Marked  
GoST-R

### Certifications

CSA Certified  
CCC Marked  
Lloyd's Register Certified

## defaultTaxonomyAttributeLabel

### Type

Light Unit

### Environmental rating

IP66, NEMA 4X, 13, Rk resistance 100

### Voltage rating

12-30 Vac/dc

### Illumination

Illuminated

### Series

M22

### Size

22.5 mm

### Actuator

Base, screw

### Light color

White

## Resources

### Brochures

[M22 Pilot Devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Installation instructions

[M22 Operators and Accessories](#)

### Specifications and datasheets

[Eaton Specification Sheet - M22-LEDC-W](#)

[Global Data Sheet - M22-LEDC-W](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)