

Eaton M22-L-W

Catalog Number: M22-L-W

Eaton M22 modular pushbutton, Indicating Light Operator, Flush, IP66, NEMA 4X, 13, Rk resistance 47, Illuminated, White, 100, 000 Hours of operation



General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-L-W

UPC

786685278612

Product Length/Depth

2 in

Product Height

1 in

Product Width

2 in

Product Weight

0.05 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked
Bureau Veritas
GoST-R

Certifications

CSA Certified
CCC Marked
Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

Type

Indicating Light

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 47

Operating Cycles

100,000 Hours of operation

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Flush

Button color

White

Light color

White

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[M22-L 3D Model Xchange](#)[M22-L 3D Inventor](#)[M22-L 2D Drawing Xchange](#)[M22-L AutoCAD 2D Footprint \(mm\)](#)[M22-L 2D PDF](#)[M22-L AutoCAD 2D Footprint](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-L-W](#)[Eaton Specification Sheet - M22-L-W](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)