

Eaton M22-C1-M1H

Catalog Number: M22-C1-M1H

M22 Assembled One Element Control Station, 22.5 mm, 40 mm Push-Pull Mushroom Head, Maintained, Non-illuminated, Button: Red, 1NC, IP66, UL (NEMA) Type 4X, 13, Horizontal, Base: Black, Enclosure: Yellow



General specifications

Product Name	Catalog Number
Eaton M22 pushbutton control station	M22-C1-M1H
UPC	Product Length/Depth
786685282916	2.83 in
Product Height	Product Width
2.7 in	3.15 in
Product Weight	Warranty
0.85 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
GoST-R	CSA Certified
CE Marked	CCC Marked
Bureau Veritas	Lloyd's Register Certified

Catalog Notes

25% smaller depth than most competitor enclosures. Impact resistant polycarbonate enclosure.

defaultTaxonomyAttributeLabel

Type

Control Station, Emergency Stop Operator

Actuator function

Maintained

Button color

Red

Actuator

40 mm push-pull mushroom head

Environmental rating

IP66, NEMA 4X, NEMA 13

Orientation

Horizontal

Contact configuration

1 NC

Enclosure color

Yellow

Illumination

Non-illuminated

Series

M22

Size

22.5 mm

Base

Black

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-C1-M1H](#)