

Eaton M22-C1-M3H

Catalog Number: M22-C1-M3H

M22 Assembled One Element Control Station, 22.5 mm, 40 mm twist-to-release mushroom head, Maintained, Non-illuminated, Button: Red, NC, IP66, UL (NEMA) Type 4X, 13, Horizontal, Base: Black, Enclosure: Yellow



Photo is representative

General specifications

| | |
|--|--|
| Product Name | Catalog Number |
| Eaton M22 pushbutton control station | M22-C1-M3H |
| UPC | Product Length/Depth |
| 786685282930 | 2.83 in |
| Product Height | Product Width |
| 2.7 in | 3.15 in |
| Product Weight | Warranty |
| 0.85 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| Compliances | Certifications |
| GoST-R | CSA Certified |
| CE Marked | CCC Marked |
| Bureau Veritas | Lloyd's Register Certified |
| Catalog Notes | |
| 25% smaller depth than most competitor enclosures. Impact resistant polycarbonate enclosure. | |

defaultTaxonomyAttributeLabel

Type

Control Station, Emergency Stop Operator

Actuator function

Maintained

Button color

Red

Actuator

40 mm twist-to-release mushroom head

Environmental rating

IP66, NEMA 4X, NEMA 13

Orientation

Horizontal

Contact configuration

NC

Enclosure color

Yellow

Illumination

Non-illuminated

Series

M22

Size

22.5 mm

Base

Black

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-C1-M3H](#)