

Eaton LSM-11S

Catalog Number: LSM-11S

Eaton LS-Titan Miniature DIN Limit Switch, Top Push Plunger, Die Cast Zinc enclosure, 6A max AC, 3A max DC, 1NO-1NC, Snap Action, Positive Opening, 6A at 240Vac, 3A at 24Vdc, Cage Clamps, ± 0.02 mm accuracy

General specifications



Product Name	Catalog Number
Eaton LS-Titan miniature DIN limit switch LSM-11S	
UPC	Product Length/Depth
786685392134	1.22 in
Product Height	Product Width
2.99 in	1.32 in
Product Weight	Warranty
0.325 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Listed

defaultTaxonomyAttributeLabel

Type

LS-Titan

Contact Rating

6A at 240Vac, 3A at 24Vdc

Accuracy

±0.02mm

Enclosure material

Die cast zinc

Connection

Cage clamps

Contact configuration

1 NO-1 NC, snap action, positive opening

Switch type

Top push plunger

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Environmental rating

IP66, IP67

Maximum AC current

6 A

Maximum DC current

3 A

Resources

Brochures

[LS-Titan Safety Limit Switches](#)

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - LSM-11S](#)