

Eaton NZMN2-VE250-BT-NA

Catalog Number: NZMN2-VE250-BT-NA

Eaton Series NZM complete molded case circuit breaker, NZM2-frame, NZMN2, Thermal-magnetic trip, Three-pole, 250A, 690 Vac, 750 Vdc, 50 kAIC, Box, Selective and gen. protect., 125-250A, Front frame clamp, 125-250A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series NZM complete molded case circuit breaker	NZMN2-VE250-BT-NA
	EAN
	4015081074952
Product Length/Depth	Product Height
5.866 in	4.134 in
Product Width	Product Weight
4.134 in	5.17 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

250 A

Voltage rating

690 Vac, 750 Vdc

Trip Type

Thermal-magnetic

Circuit breaker type

NZMN2

Terminals

Box

Frame

NZM2

Class

Selective and generator protection

Accessories

Rocker lever, motor drive

Adjustment range short-circuit release

250-2500A delayed, 3000-3000A delayed

Setting Range OI Protector

125-250A

Short-circuit breaking capacity

50 kAIC

Interrupt rating

50 kAIC

Connection

Front frame clamp

Overload range

125-250A

Number of poles

Three-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - NZMN2-VE250-BT-NA](#)

[Product Data Sheet - NZMN2-VE250-BT-NA](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)