

Eaton NZMH2-AF50-BT-NA

Catalog Number: NZMH2-AF50-BT-NA

Eaton Series NZM complete molded case circuit breaker, NZM2-frame, NZMH2, Adj. thermal, fixed magnetic trip, Three-pole, 50A, 690 Vac, 750 Vdc, 85-150 kAIC, Box, Distribution circuit protect., 50-50A, Front frame clamp, 50-50A

General specifications



Photo is representative

Product Name

Eaton Series NZM complete molded case circuit breaker

Catalog Number

NZMH2-AF50-BT-NA

EAN

4015081074631

Product Length/Depth

4.05 in

Product Height

7.24 in

Product Width

4.13 in

Product Weight

4.1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Amperage Rating

50 A

Voltage rating

690 Vac, 750 Vdc

Trip Type

Adjustable thermal, fixed magnetic

Circuit breaker type

NZMH2

Terminals

Box

Frame

NZM2

Class

Distribution circuit protection

Accessories

Rocker lever, motor drive

Adjustment range short-circuit release

300-500A delayed

Setting Range OI Protector

50-50A

Short-circuit breaking capacity

150 kAIC

Interrupt rating

85-150 kAIC

Connection

Front frame clamp

Overload range

50-50A

Number of poles

Three-pole

Resources

Specifications and datasheets

[Product Data Sheet - NZMH2-AF50-BT-NA](#)

[Eaton Specification Sheet - NZMH2-AF50-BT-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)